

## **Lola T Prestige**

Sunlounger

Technical file















Description

## **Frame**

Made of polypropylene resin.

Reinforced with mineral filler and a special formulation with UV treatment.

Ribbed design that guarantees structural robustness against deformation and breakage.

## **Security**

Folding support designed to prevent hands and fingers from being caught.

Support regulator designed to avoid sudden movements during height regulation.









# **Lola T Prestige**

## Sunlounger

## Capacity

Package

B A	
A - 75 cm	C - 198 cm

4 - /5 cm	C - 198 cm
3 - 95 cm	D - 37 cm

14,6 kg

Box	2 u.	201x78,5x63 cm	35,8 kg	1,00 m³
Pallet	14 u.	200x74x178 cm	312 kg	2,78 m <sup>3</sup>

Measures

Units

Loading capacity	Mega trailer	Cont. 20'	Cont. 40'	Cont. 40' High Cube
Lola T Prestige	520 u.	160 ц	330 u.	400 u

## **Finishes**

## Frame

## Matte texture







## Slats

## Basic





Weight

Volume









## **Lola T Prestige**

Sunlounger

Maintenance plan	

## Weekly

Visual check of the general condition, removing dirt and ensuring there are no broken parts or damage that could be a danger to users.

#### Monthly

Check the structural strength and stability.

Check the condition of wheels.

#### **Annual**

Check the backrest and adjuster are working correctly.

Replace any worn or damaged parts.

## Wintering and storage

Clean with soapy water and a soft cloth.

Remove damp stains, sand and seawater.

Store horizontally in a dry place in stacks of 10 units.

## **Observations**

- Always use Balliu spare parts.
- Balliu does not manufacture parts for other brands.
- If the product is subject to heavy use, maintenance checks must be carried out more frequently.
- Do not use the product until maintenance is completed.
- Consult the maintenance instructions.
- Do not use aggressive chemicals to clean the product.
- Always use products with a neutral pH.
- Use a soft cloth to clean the product.





